

Cila イメージングエキスパート株式会社

産業用LED照明装置



Catalog 2014/2015

Cila イメージングエキスパート株式会社

営業・技術サポートセンター

03-6686-3225

メール: sales_support@cila-japan.com

<http://www.cilaimagingexpert.jp>



LATAB

産業用LED照明装置

スレッドレンズ 付きリング照明


This ring light can be easily mounted in two ways:

- By a small bracket (order no. LAD3 7218)
- By a standard lens adapter with a lens thread of 37 x 0.75 mm. Various threads are available to fit different lenses

The best evenness of light will be achieved at a working distance of 20-25 mm. A diffuser is included.



Mechanical dimensions



Step files available on request

Order information

Order number	Sizes (mm)		Working distance (mm)	Controller ¹⁾	
	outer ϕ	inner ϕ		steady mode	strobe mode
SAX3 1044	44	29	20-25	1 A	8 A

¹⁾ See controller selection for details


Color information

Replace "X" in order number by one character ²⁾	Color	Wavelength
H	Red	617 nm
W	White	
R	IR	880 nm
B	Blue	465 nm
G	Green	520 nm
U	UV	395 nm

²⁾ Example for red ring light: SAH3 1044

Options

- Cable length and type see "Order options"
- Lens adapters for different lens threads on request
- Bracket LAD3 7218:






LATAB

産業用LED照明装置



Customer-specific developments and adaptations are a core part of LATAB's business at near standard prices of course, and with short project lead times. You name it, we'll make it!

Design skills:

- CAD engineering
- Electronics development
- Thermal management



Customer-specific circular back light with 3 camera holes



In addition to LED lighting for the machine vision market, LATAB also offers general lighting solutions.

Examples include decorative lighting and object illumination, both indoors and out, using light modules based on high brightness or ultra-bright LEDs. LATAB's extensive experience in meeting the requirements of industrial applications paired with many years of design skills are the key to its successful LED engineering.



Cila イメージングエキスパート株式会社
営業・技術サポートセンター
03-6686-3225
メール: sales_support@cila-japan.com
<http://www.cilaimagingexpert.jp>